

SOLBERG RE-HEALING RF1-AG 1% Foam Concentrate

Class B | Fluorine-Free Foam

Product Overview

SOLBERG® RE-HEALING™ RF1-AG, 1% foam concentrate from SOLBERG is an innovative environmentally sustainable fluorosurfactant and fluoropolymer-free foam concentrate used to effectively extinguish Class B hydrocarbon fuel fires. Proportioned at 1% solution, SOLBERG RE-HEALING RF1-AG foam concentrate can be used in fresh and salt water. SOLBERG RE-HEALING RF1-AG foam concentrate possesses excellent burn back resistance due to its remarkable flow and rapid resealing characteristics. SOLBERG RE-HEALING RF1-AG foam concentrate is formulated using a new high performance synthetic foam technology to replace traditional AFFF, FFFP foam concentrates and older protein and fluoroprotein foams.

Performance

Fire Performance

SOLBERG RE-HEALING RF1-AG foam concentrate has been tested to and meets the fire performance test criteria of European Standard EN 1568 Part 3 (latest edition).

Foam Proportioning

SOLBERG RE-HEALING RF1-AG foam concentrate can be proportioned at the proper foam solution percentage using common foam proportioning devices such as:

- Eductor
- Inline balanced pressure proportioners
- Ratio controllers
- Self-educing nozzles



Storage

The storage temperature range for SOLBERG RE-HEALING RF1-AG foam concentrate is -24°C to 50°C (-11°F to 122°F).

When stored in original containers or in manufacturer recommended equipment and within the specified temperature range, the shelf life is 20 years.

Typical Physicochemical Properties AT 25 °C (77 °F)

Appearance	Clear, yellow-orange liquid
Freezing Point	-24°C (-11°F) (No quality loss after thawing)
Maximum Storage Temperature	50°C (122°F)
pH	7.0 - 8.5
Refractive Index	1.4580 - 1.4680
Specific Gravity	1.120 - 1.130
Viscosity	< 20 cSt* *Cannon-Fenske Viscometer
Sediments	< 0.05%

Applications

SOLBERG RE-HEALING RF1-AG foam concentrate is intended for use on Class B hydrocarbon fuel fires. It is not intended for use on Class B polar solvent fuels. The foam can be used to prevent re-ignition of a liquid spill and control hazardous vapors. On Class A fuels, SOLBERG RE-HEALING RF1-AG foam will improve extinguishment in deep-seated fires. Foam discharge devices such as air aspirating, as well as non-air aspirating equipment can be used to obtain maximum results. The product is mixed 1 part foam concentrate to 99 parts water. It may also be used as a 1% pre-mix solution. SOLBERG RE-HEALING RF1-AG foam is compatible with most dry powder (chemical) agents.

SOLBERG RE-HEALING RF1-AG 1% Foam Concentrate

Class B | Fluorine-Free Foam



Inspection

SOLBERG RE-HEALING RF1-AG foam concentrate or pre-mix solution should be inspected annually per National Fire Protection Association (NFPA) Standards 11 and 25. A sample of the foam concentrate should be sent to the manufacturer for quality conditioning testing in accordance to NFPA 11.

Compatibility

SOLBERG RE-HEALING RF1-AG foam concentrate should not be mixed with other foam concentrates. For questions about compatibility or mixing, consult Perimeter Solutions Technical Services.

Materials of Construction Capability

SOLBERG RE-HEALING RF1-AG foam concentrate is compatible with multiple materials of construction such as carbon steel, stainless steel, brass, polyethylene and PVC. Galvanized steel should not be used in direct contact with the foam concentrate. For questions about materials of construction compatibility, consult Perimeter Solutions Technical Services.

Environmental Information

SOLBERG RE-HEALING foam concentrates do not contain intentionally added PFAS chemicals including PFOA and PFOS. In making this statement, SOLBERG relies on information provided by its raw material suppliers and certain independent laboratory analysis conducted on the product.

Certifications

SOLBERG manufactured products are thoroughly inspected and undergo rigorous quality control tests. These evaluations analyze the foam's physical parameters as well as the finished product's fire performance. A Certificate of Analysis (CoA) is issued with every batch. SOLBERG RE-HEALING RF1-AG foam concentrate is European Standard EN 1568 Part 3 Approved.

Ordering Information

SOLBERG RE-HEALING RF1-AG foam concentrate is available in pails, drums, totes and bulk quantities.

Part Number	Description	Approximate Shipping Weight	Approximate Cube
20840	SOLBERG RE-HEALING RF1-AG, 1% - 5 gallon (20 litre) pail	21 kg (45 lb)	0.04 m ³ (1.25 ft ³)
20841	SOLBERG RE-HEALING RF1-AG, 1% - 55 gallon (200 litre) drum	224 kg (495 lb)	0.33 m ³ (11.83 ft ³)
20842	SOLBERG RE-HEALING RF1-AG, 1% - 265 gallon (1000 litre) tote	2465 kg (1118 lb)	1.42 m ³ (50.05 ft ³)
20843	SOLBERG RE-HEALING RF1-AG, 1% - bulk	Call Customer Services	

www.frsa.com.au | admin@frsa.com.au | + 61 7 3209 7422

